


Product Code: CMA652-CH
Description: 13A Double Pole Switched Fused Connection Unit With Neon - Fused, Cooker Hood

Luckinslive 438962325



General Information

Plate Dimensions (mm)	86 (W) x 86 (H) x 9.5 (D)	
Plate Fixing Centres - Horizontal (mm)	60.3	
Style	Rounded Profile	
Colour	Polar White	
Materials	Front Plate, Rocker Switch & Fuse Drawer: Urea	Rear Housing: Urea
	Neon Lens: Polycarbonate	Terminals: Brass
	Terminal Screws: Steel & Yellow Passivated	Contacts: Silver "on-lay" Copper / Brass
	Internal Busbars: Formed Pressed Brass	Earth Strap: Mild Steel
Anti Microbial Certified	Yes	
Operating Voltage (AC)	250	Frequency (Hz) 50
Resistive Load Rating (A)	13	
Fuse Fitted Type	Plug Top Cartridge Fuse	
Termination Type	Screw	
Terminal Size (mm)	Ø5	Terminal Torque Value (Nm) 2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4	
Switched	Yes	
Double Pole Switch	Yes	
Twin Earth Terminals	Yes	
Neon Indicator	Yes	Indicator Colour Orange
Product Marking	Fused, Cooker Hood	
Minimum Back Box Depth (mm)	25	
Ingress Protection	IP20	
Operational Temperature (°C)	-5 to +40	
Warranty (Years)	25	

Standards BS 1363-4, BS 1362

Additional Information

For cleaning / polishing of products, use only a soft, dry, clean cloth.
Ensure that the mains supply is isolated before commencing installation and refer to the circuit diagram with the relevant product.
Bare earth cables must always be covered with appropriate sleeving and wired to the earth terminal.
All white moulded accessories are manufactured using Urea Formaldehyde, which has similar inherent properties to antimicrobial additives that inhibit the growth of infectious diseases as well as anti-viral properties against enveloped and non-enveloped viruses.
All products have been independently tested with 99.9% of enveloped viruses and 92% of non-enveloped viruses killed off whilst achieving a 99.9% kill rate across all four types of the strains of bacteria - MRSA, E-Coli, Salmonella, and Klebsiella Pneumoniae.



CLICK OR SCAN

Catalogue



Range



DoC



Installation



CLICK OR SCAN